Cherry Burrell Stellar-Flo Homogenizer - 300 PSI	
Mfg: Cherry Burrell	Model: SS-200
Stock No: MABE002B	Serial No: 79019

Cherry-Burrell Stellar-Flo Pump. Model 200. S/N: 79019. Plunger size: 5/8 in. Capacity: 45/22.5 US Gal. / Hr. Maximum Operating Pressure: 300 PSI. Sterling variable speed drive: 5 HP, 230/460V, 13.0/6.5 Amps, 60 Hz, 3-phase, 204-1430 RPM. \*Note: This unit was previously used in a non-food grade application. The motor also appears to have been changed to 208V, 13 Amps, 3-phase. (H)

