

Pressurized Steel Storage Tank with Agitator – 2000 Gallons

Mfg:

Model:

Stock No: MASH061

Serial No:

Pressurized Steel Storage Tank with Agitator. Approximate capacity: 2000 gallons. Reliance Electric motor: 5 Hp, 1160 Rpm, 230/460 V, 15.6/7.8 A, 60 Hz, 3 Phase. Agitator with Browning speed reducer, model: A, ratio 15:1. Top manway: 22 in. OD, 18-1/2 in. ID., with (20), 1/2 in mounting holes. Lid has a 5 in. threaded input, 1-1/4 in. input with ball valve and a 1 in. input. (2) 2.5 in. outlets. Overall dimensions: 7 ft. L x 5 ft. 8-1/2 in. W x 11 ft. 10 in. H.





