

## APV / Crepaco Positive Displacement Pump

Mfg: APV / Crepaco

Model: 6R

Stock No: MDBC033.4

Serial No: 8052

APV / Crepaco R-series Positive Displacement Pump. Model: 6R. S/N: 8052. APV / Crepaco R-series pumps are known for their rugged, long-lasting, efficient performance. Every pump in the line has as standard a stainless steel body. Economical service over a wide range of products and applications, easy disassembly and cleanup, low maintenance. U.S. electric motor, 5 hp, 1140 rpm, 208-220/440 V, 15.8-15.0/7.5 amps, 60 Hz, 3 phase. Driver Pulley: 6-3/4 in. Dia. Driven Pulley: NO PULLEY. Ratio: 2.83. Final rpm: 403. Inlets/outlets: (2) 2-1/2 in. dia. ACME fittings. Overall dimensions: 3 ft. 5-1/8 in. L x 1 ft. 4-3/4 in. W x 2 ft. H.





