

APV/Crepaco Centrifugal Pump

Mfg: APV/Crepaco

Model: 6V2

Stock No.: MDBC120.1a

Serial No.: H-1137-93

Crepaco Centrifugal Pump. Model: 6V2. S/N: H-1137-93. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 6 in. Reliance electric motor, 5 hp, 1730 rpm, 230/460 V, 14.0/7.0 amps, 60 Hz, 3 phase. Inlet: (1) 2 in. ACME fitting. Outlet: (1) 1-1/2 in. ACME fitting. Overall dimensions: 1 ft. 10 in. L x 1 ft. W x 1 ft. H. (ACN27a)



