

Lincoln Electric Co. Motor – 30 hp


Mfg: Lincoln Electric Co.

Model:

Stock No: MDBC257B

Serial No: 509971

Lincoln Electric Co. Motor – 30 hp. Motor specifications:, Frame 326-U, Volts 230/460, Phase 3, Hz. 60/50, Amps 71/35.5 - 76/38, Type DG, NEMA Code F, Design B. Lincoln Code: V 1388, RPM 1745/1450 Hz.60/50, Amps 71/35.5 - 76/38, Shaft diameter 1-7/8in. Overall dimensions L 2ft. 4in. x W 2ft. 4in. x H 1ft. 9in. (BB)





LINCOLN MOTOR

LINGGUARD

FRAME	326-U	SERIAL	508971				
H.P.	30	PH.	3	TYPE	DG	TIME RATING	CONT.
VOLTS	480/460	DESIGN	B				
NEVA CODE	F	LINCOLN CODE	V 1388				
80	CYCLES	50					
1745	RPM	1450					
7	AMPS	76/38					
40	*C RISE	50					
1.15	SERV FACT	1.0					

LOW VOLTAGE LINE: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

HIGH VOLTAGE LINE: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10

THE LINCOLN ELECTRIC CO. MADE IN U.S.A.