

Lincoln A.C. Motor 50hp

Mfg: Lincoln

Model:


Stock No: MDBC260B

Serial No: 3754415

Lincoln electric motor: 50 hp. Motor specifications: RPM 1770, Frame 326T, Volts 230/460, Phase 3, Hz.60, Amps 125/62.5, INS Code F, NEMA Code G, NEMA Design B. Shaft diameter 2in. Overall dimensions L 2ft. 3in. x W 1ft. 9in. x H 1ft. 6in. (BB)





LINCOLN  **LINGUARD**
A.C. MOTOR **DRIPPROOF**

HP 5.0 RPM 1770 FRAME 326T

VOLTS 230/460 PHASE 3 HERTZ 60

AMPS 125/62.5 TIME RATING CO

CAN BE USED ON _____

MAY NOT MEET ALL NEMA 1 RECOMMENDATION LIMITS ON 208V SYSTEM UP TO _____

INSULATION CLASSIFICATION _____

NEMA FRAME FACTOR _____

NEMA CODE _____

NEMA DESIGN _____

NOMINAL EFFICIENCY _____

LE CO. _____

DATE _____

ERL _____

637636

LOW VOLTAGE LINE

↑ 1 ↑ 2 ↑ 3
 ● 12 ● 10 ● 11
 ● 6 ● 4 ● 5
 ● 7 ● 8 ● 9

HIGH VOLTAGE LINE

↑ 1 ↑ 2 ↑ 3
 ● 12 ● 10 ● 11
 ● 7 ● 5 ● 8 ● 6 ● 9