

Lincoln A.C. Motor 100hp

Mfg: Lincoln

Model:

Stock No: MDBC261B

Serial No: 3739448

Lincoln electric motor: 100 hp. Motor specifications: RPM 1770, Frame 404-T, Phase 3, Volts 230/460, Hz.60, Amps 238/119, Can be used on 208V system up to 269 AMPS. INS NEMA F, NEMA Code G, NEMA Design B., Shaft diameter 2-7/8in. Overall dimensions L 2ft. 9in. x W 2ft. 4in. x H 2ft. (BB)



