

## Trenton Refrigeration 3-Fan Evaporator Unit – 1 Ton



Mfg: Trenton Refrigeration





Model: TLP105DED



Stock No.: MDBC306



Serial No.: 030105888


Trenton Refrigeration 3-Fan Evaporator Unit. Model: TLP105DED. Serial number: 030105888. Rated capacity: 12,390 BTUH at 20°F with a 10°F TD. Displacement: 2,400 cfm. Electric defrost with 3,550 watt heater. Power supply: 208/230 V, 19.3/13.1 amps, 3550 watts, 1/3 phase. (3) Fan motors: 1/20 hp, 208/230 V, 1 amp, 60 Hz, single phase. Fan blade diameter: 13 in. Inlets: (1) 1 in. diameter port. Outlets: (1) 3/4 in diameter port. Estimated weight: 118 lbs. Overall dimensions: 5 ft. 9 in L x 1 ft. 4 in. W x 1 ft. 4-3/4 in. H. (ACN14a).











**UNIT COOLER**

MODEL TLP105DED SERIAL # 838105888

UNIT ENTERING ELECTRICAL SERVICE




FAN MOTORS:		VOLTS	PHASE	HZ	MIN AMPACITY	MAX OVERCURRENT PROTECTION
208/230		1		3550	13.3	25
208/230		3		3550	13.1	15


DEFROST HEATERS:		VOLTS	PHASE	TOTAL WATTS	MIN AMPACITY	MAX OVERCURRENT PROTECTION
208/230		1		3550	13.3	25
208/230		3		3550	13.1	15

FAN MOTORS:	QTY	VOLTS	PHASE	HZ	FLAT/FLA	HP/EA
	3	208/230	1	50	1.0	1/20

DEFROST HEATERS:	QTY	VOLTS	PHASE	WATTS/EA
	3	230	1	750
	1	230	1	1300

FACTORY CHARGE: DRY AIR HOLDING  
 FOR USE WITH: R12, R22, R502, R134a, R404A, R407C & R507  
 DESIGN WORKING PRESS. 300 P.S.I.G.  
 TESTED PRESSURE 300 P.S.I.G.


 NATIONAL REFRIGERATION AND AIR CONDITIONING CANADA CORP.  
 100 WEST 85th ST. BRANTFORD, ONTARIO  
 CANADA N6B 1K1

MADE IN CANADA