

Baader Fish Skinning Machine

Mfg: Baader

Model: 47

Stock No: MDFC038.3a

Serial No: 10 6209 0047

Baader Fish Skinning Machine. Type 47. S/N: 10 6209 0047. Nominal capacity (depending on fillet length): 60 fillets/minute. Largest fillet: 8-21/32 in. (22 cm). The machine is design for the skinning of fillets from white fish, redfish and flat fish. Skin is removed leaving the iridescent sliver glaze on the fillets. (2) Adjustable angle conveyors. Fillet feeding belt conveyor: 4 ft. L x 8 in. W. Infeed/exit height: 3 ft. 1-1/4 in. Fillet discharge stainless steel conveyor: 2 ft. 7-1/4 in. L x 8 in W. Infeed/exit height: 3 ft. 1 in. Siemens electric motor, 1410/1660 rpm, 220/380 V, 5.35/3.1/ 5.5/3.2, 50/60 Hz, 3 phase. Water connection: 1/2 in. Water consumption: approximately 2 gallons/min. Approximate weight: 585 lbs. Overall dimensions: 7 ft. 1 in. L x 2 ft. 10-1/2 in. W x 3 ft. 7 in. H.









BAADER	
NORDISCHER MASCHINENBAU RUD. BAADER · GMBH + CO KG · LÜBECK	
Typ	47
Baujahr	1984
Masch. Nr.	10 6209 0047
Leistung	1.3 KW
Anschlußspg.	220 V3~
Frequenz	60 Hz
Steuer spg.	V~ mit ohne Trafo
Betriebsspg.	220 V3~
	V~
	V~
Nennstrom	5.5 A
Stromzufpl. - Nr.	047 59 2 1 000
MADE IN GERMANY	

