

Carlyle 6-Cylinder Freon Compressor

Mfg: Carlyle

Model: 06 CY 550E- 103

Stock No: MDFC216.1

Serial No: 1696HE 1828

Carlyle 6-Cylinder Freon Compressor. Model: 06CY550E-103. S/N: 1696ME1828. Motor: 06ED-445-314, 1800 rpm, 142 amps, 208/230 V, 60 Hz. 3 Phase. Remanufactured SA 8635. Voltage 264 does not exceed 528. Nor is 187 less than 414. (LS/HS) 315/2174. TEST: (PSI/KPa) 450/3105. The first stage utilizes four cylinders and always operates at a low compression ratio. Two additional cylinders act as the high stage, completing the compression cycle at discharge temperatures much lower than a single-stage compressor. Lower discharge temperatures result in increased reliability. Inlet/Outlet: (2) 3 in. dia. ports. Overall Dimensions: 2 ft. 7 in. L x 1 ft. 9 in. W x 1 ft. 9 in. H.



