

**Ariens ST8 Gas Powered Snow-blower – 24 in.**

**Mfg: Ariens**

**Model: ST824 (924082)**

**Stock No: MDFC220**

**Serial No: 027231**

Ariens 24 in. Gas Powered Snowblower. Model: ST824 (924082). S/N: 027231. This mid-range Ariens brand snow-blower is ideal for home in the country. The 8 hp Tecumseh® Snow King engine provides plenty of get-up-and-go while a hungry auger and impeller unit cuts extra-wide paths through snow-covered sidewalks and driveways. The quick-turn chute rotation, and 220° directional control, enables you to throw snow away from your cleared area. The 824 comes with six forward and two reverse speeds. Clears approx. 23 in. wide path. Auger Impeller dimensions: 23-1/2 in W x15-1/4 in. dia. Output: 5-7/8 in. dia port. Overall dimensions: 4 ft. 8 in. L x 2 ft. 3/8 in. W x 3 ft. 7 in. H. (ACN13).





