

Allen-Bradley 2 HP Variable Speed Controller

Mfg: Allen-Bradley

Model: 161S-AA07NPU Series B

Stock No: MDFF050.3a

Serial No: 014AT1998300131

Allen-Bradley 2 HP Variable Frequency Drive. Model: 161S-AA07NPU. S/N: 014AT1998300131. Input: 200-240V, 16.0 (9.3)A, 50/60 Hz. Output: 200-230V, 7.1A. Mass: 3.4 Kg., 0.5-360 Hz. Motor rating: 1.5 KW/ 2 HP. Mounting holes center to center on width: 4 in. Mounting holes center to center on height: 6- $\frac{3}{4}$ in. Overall dimensions: 6 in.L X 4- $\frac{3}{8}$ in. W X 7 in. H.



161S-AA 07NPU

SERIES B

FRN: 2.001

**I
N
P
U
T**
V: 200-240 1 ϕ (3 ϕ)
A: 16.0(9.3)
Hz: 50/60
VA: 2900

**O
U
T
P
U
T**
V: 200-230 3 ϕ
A: 7.1
Hz: 0.5-360
Motor
Rating: 1.5KW/ 2HP

POWER TERMINAL WIRE
Use 75°C Cu Wire
5.3-2.1 mm² (10-14 AWG)
Torque 1.3 Nm (11.5 in.-lbs.)

S/N: 014AT1998300131

Date: 0005 NE17103 S



Allen-Bradley IP20

MADE IN JAPAN