

Hansen Technologies Auto-Purger

Mfg: Hansen Technologies

Model: APC

Stock No: MDFF363.8a

Serial No: N2609

Hansen Technologies Auto Purger. Model: APC. Serial no. N2609 Single point purger. Receiver- 1.5 Gallon, straight-wall dimensions: 5 in. dia. x 1 ft. 8 in. L. (5) Hansen Technologies Solenoids, power supply: 115 V, 60 Hz, 16 watts. Hansen Float Switch, power supply: 120/240 VAC, 3 amps, max temperature: 150°F, min. temperature: -50°F. Inlets: (1) 1/2 in. dia. high pressure liquid port, (1) 1/2 in. dia. foul gas port, (1) 1/2 in. dia. water line port. Outlets: 3/4 in. dia. suction line port, (1) 1 in. dia. drain to sewer port. Overall dimensions: 3 ft. 1/2 in. L x 1 ft. 9 in. W x 3 ft. 11 in. H.



