

Saftronics, Inc. Variable Speed Controller

Mfg: Saftronics, Inc.

Model: GP10E4ST34F50B1

Stock No: MDFP043B

Serial No: 0123-05696N0008

Saftronics Variable Speed Controller. Model: GP10E4ST34F50B1. S/N: 0123-05696N0008. Input: 380-480 V, 1.63 amps, 50/60 Hz, 3 phase. Output variable / constant TQ: 0.5 hp, 380-460 V, 0.1-120 Hz, 1.5 amps.





Model No. GP10E4ST34F50B1
Serial No. 0123-05696N0008

SAFTRONICS **GP10** Part No. GP104F50-4

Model No. GP10E4ST34F50B1
Serial No. 0123-05696N0008

UL US LISTED
IND. CONT. EQ
7898 **CE**

Input		Output Variable TQ	Output Constant TQ	
Volts	380-480	0.5	Hp	0.5
Amps	1.63	380-460	Volts	380-460
Freq (Hz)	50/60	0.1-120	Freq Range (Hz)	0.1-120
Phase (s)	3	1.5	Amps	1.5
		110%	Over Load (1 min)	150%

NEMA Enclosure Type : 4
Instruction Book : 027-GP1001

SAFTRONICS INC.
Made in Mexico

