

Safetronics, Inc. Variable Speed Controllers


Mfg: Saftronics, Inc.

Model: GP10E4ST34003B1

Stock No: MDFP044.1a

Serial No: 0133-06655N0005, 0126-05701N0018

(2) Safetronics, Variable Speed Controllers Inc. Model: GP10E4ST34003B1. SN: 0133-06655N0005, 0126-05701N0018. Input: 380-480V, amps: 8.61. Freq: 50/60, 3 phase. Output constant / variable: 3 hp, 380-460V, 5.5 amps, 0.1-120 Hz. NEMA 4 enclosure. Overall dimensions: 6 in. L x 5-1/2 in. W x 10 in. H.



Model No. GP10E4ST34003B1
Serial No. 0126-05701N0018

SAFRONICS

GP10

Part No.
GP104003-4

Model No. GP10E4ST34003B1
Serial No. 0126-05701N0018



Input		Output Variable TQ	Output Constant TQ	
Volts	380-480	3	HP	3
Amps	8.61	380-460	Volts	380-460
Freq (Hz)	50/60	0.1-120	Freq Range (Hz)	0.1-120
Phase (s)	3	5.5	Amps	5.5
		110%	Over Load (1 min)	150%

NEMA Enclosure Type : 4
Instruction Book : 027-GP1001

SAFRONICS INC.
Made in Mexico

Model No. GP10E4ST34003B1
Serial No. 0133-06655N0005

SAFRONICS

GP10

Part No.
GP104003-4

Model No. GP10E4ST34003B1
Serial No. 0133-06655N0005



Input		Output Variable TQ	Output Constant TQ	
Volts	380-480	3	HP	3
Amps	8.61	380-460	Volts	380-460
Freq (Hz)	50/60	0.1-120	Freq Range(Hz)	0.1-120
Phase(s)	3	5.5	Amps	5.5
		110%	Overload (1min)	150%

NEMA Enclosure Type : 4
Instruction Book : 027-GP1001

SAFRONICS, INC.
Made in Mexico