

Vilter VMC 450XL 8-Cylinder Reciprocating Compressor - 150 HP

Mfg: Vilter

Model: 458XL

Stock No: MDOF241.40

Serial No: 66033

Vilter VMC 450XL 8-Cylinder Reciprocating Compressor - 150 HP. Model: 458XL. Serial No: 66033. Order No.: K-09748. Number of cylinders: 8. A12K458XLB. Test pressure: 525 PSI high side, 375 PSI low side. Lincoln Motor Drip Proof Motor, Serial # 316645. 150 HP, 1780 RPM, 460 Volts, 169 Amps, 60 Hz, 3-phase, 444T Frame. Square D size 5 starter included, no enclosure. Overall dimensions: 92 in. L x 45 in. W x 77 in. H.



