

Vilter VMC 450XL 8-Cylinder Reciprocating Compressor - 150 HP

Mfg: Vilter


Model: 458XL


Stock No: MDOF242.40

Serial No: 66327

Vilter VMC 450XL 8-Cylinder Reciprocating Compressor - 150 HP. Model: 458XL. Serial No: 66327. Order No.: K-24160-2. Number of cylinders: 8. A12K458XLB. Test pressure: 525 PSI high side, 375 PSI low side. Baldor Motor, Cat # M2558T-4, Spec # 18D0001W979H1. 150 HP, 460 Volts, 175 Amps, 1780 RPM, 60 HZ, 3-phase, 444T Frame. Square D size 5 starter included, no enclosure. Overall dimensions: 92 in. L x 45 in. W x 77 in. H.





 **NEMA SIZE 5**
SQUARE D COMPANY

CLASS	TYPE	THREE-PHASE RATING	
		VOLTS AC	MAX. HP
8536	SGD 3	200	75
		230	100
		380	150
		460/575	200

MADE IN U.S.A. 600V MAX 86