

Vilter VMC 450XL 6-Cylinder Reciprocating Compressor - 100 HP

Mfg: Vilter

Model: 456XL

Stock No: MDOF243.37

Serial No: 66095

Vilter VMC 450XL 6-Cylinder Reciprocating Compressor - 100 HP. Model: 456XL. Serial No: 66095. Order No.: K-12260. Number of cylinders: 6. Size: 11K456XL. Test pressure: 525 PSI high side, 375 PSI low side. Toshiba High Efficiency Motor, Model # B1004VLF3UM, Serial # 91YO7762. 100 HP, 230/460 Volts, 248/124 Amps, 1770 RPM, 60 HZ, 3-phase, ENCL DP. Furnas brand size 5 starter included, no enclosure. Overall dimensions: 92 in. L x 45 in. W x 77 in. H.



