

APV Crepaco Stainless Steel Jacketed Process Tank with Shear Mixer – 150 Gallons

Mfg: APV Crepaco

Model:

Stock No: MDPK519.27a

Serial No: B-0832

APV Crepaco Dome-Top Stainless Steel Dimple Jacketed Process Tank with Shear Mixer. Rated capacity: 150 gallons. Material of construction: 304 stainless steel. Maximum rated working pressure: 50 PSI. Features an interior dimpled wall, 4 in. spray ball and a 12 in. diameter shear mixer on a 29 in. x 1-1/4 in. shaft, driven by a continuous operable motor: 2 hp, 1730 rpm, 230/460V, 4/3.2 amps, 60 Hz, 3 phase. Top inlets include: 18 in. diameter main opening, a 2-1/4 in. vapor vent, (2) 2-1/4 in. ID threaded, (1) 1-1/4 in. ID threaded attached to the spray ball. (1) 2-1/2 in. bottom outlet. Overall dimensions: 3 ft. 11 in. L x 3 ft. 11-1/2 in. W x 6 ft. 10 in. H.





