

## McQuay Air Cooled Water Chiller-220 Tons

Mfg: McQuay

Model: ALS220A

Stock No. MQI004

Serial No. 56K8146201


McQuay Air Cooled Water Chiller- 220 Ton. Model ALS220A, S/N 56K8146201.

(2) Compressors. Pressure: 450 psig (max relief), 380 psig (high side test), 150 psig (low side test).

Refrigerant: R 22. Charge: 440 lbs (total), 140 lbs (circuit 1), 150 lbs (circuit 2), 150 lbs (circuit

3). Power supply: 460 V, 60 Hz, 3 phase. Minimum branch circuit ampacity: 460 amps. Max branch circuit fuse size: 500 amps. Overall dimensions: 356 in. L x 84 in. W x 95 in. H.







**McQuay** INTERNATIONAL

AIR-COOLED CONDENSING UNIT  
 AIR-COOLED WATER CHILLER

MODEL NO. \_\_\_\_\_  
SERIAL NO. \_\_\_\_\_

COMPRESSOR	HT	A.P. S.A.	RLA	L.A.M.T.S.	S.O.L.T.E.A.C.H.	HIGH RELIEF PRESSURE	NO. PSI
COMPRESSOR			RLA			HIGH SIDE TEST PRESSURE	NO. PSI
COND. FAN MOTOR			FLA			LOW SIDE TEST PRESSURE	NO. PSI
COND. FAN MOTOR			FLA			REFRIGERANT	LB
DRYER/CLAP NETS			A			TOTAL CHARGE	LB
DRYER/CLAP NETS			A			CIRCUIT 1 CHARGE	LB
DRYER/CLAP NETS			A			CIRCUIT 2 CHARGE	LB
DRYER/CLAP NETS			A			CIRCUIT 3 CHARGE	LB

FACTORY CHARGED

MINIMUM BRANCH CIRCUIT AMPACITY	AMP	AMP
MINIMUM BRANCH CIRCUIT FUSE SIZE	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #1	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #2	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #3	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #4	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #5	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #6	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #7	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #8	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #9	AMP	AMP
MULTIPLE POWER SUPPLY ELECTRICAL CIRCUIT #10	AMP	AMP

NOTE: FOR OUTDOOR USE, THERMALLY PROTECTED SYSTEM.

CHILLER 1



NAT'L BD. 30581

Certified by: **McQuay International**  
 Staunton Operations

REFRIG. SIDE TYPE OF CONSTR. \_\_\_\_\_  
 WATER SIDE TYPE OF CONSTR. \_\_\_\_\_

MAWP	PSI @	100	T	PSI @		T
MDMT	T @	200	PSI	T @		PSI

YEAR BUILT 2010 SERIAL 0000000000  
 STYLE 0000000000 MODEL 0000000000  
 CEN 0000000000

71961001-ME      MERVILLE, MN. 55440  
 MADE IN U.S.A.