

2005 McQuay Air Cooled Water Chiller- 25 Ton

Mfg: McQuay

Model: ACZ025A27-ER11

Stock No. MQI301.33

Serial No. STNUENG082905.

2005 McQuay Air Cooled Water Chiller- 25 Ton. Model: AGZ025AS27-ER11. S/N: STNUENG082905. Refrigerant: R-22. Maximum relief pressure: 450 psig. MAWP hi/lo: 450/150 psig. Total refrigerant charge: 36 lbs. (2) Copeland Scroll Compressors, Model: 2R16M3-TWD-570, S/N's: 00K66752G and 99195362G, 3,500/2,900 rpm, 460/380-420 V, 158/151-167 LRA, 60/50 Hz, 3 phase. Inlets/outlets: (2) 2 in. dia. NPT (male). Overall dimensions: 9 ft. L x 47 in. W x 51 in. H. (2) 26 in. diameter fans with Century AC Motors, 1.0 hp, 1140/940 rpm, 460/208-230, 1.8/3.6-3.7 amps, 60/50 Hz. (2) Compressors 21.8 RLA. (3) Condenser fan motors, 2.8 FLA. (1) Evaporator heater, 0.87 amps. (2) Crankcase heaters 0.61 amps. Min. ckt ampacity: 58 amps. Max fuse ckt breaker 80 amps. MicroTech II controller.

