

Ametek Rotary Drum Filter


Mfg: Ametek

Model:

Stock No. 25.MRD263a.4

Serial No. LZ-56036-3

Ametek Rotary Drum R.H. Filter. S/N: LZ-56036-3. Size: 20 in. L x 24 in. W. Speed: 1 min 6 max. (12) $\frac{3}{4}$ in. dia. feed tubes. Reliance Electric Motor, $\frac{1}{2}$ hp, 1725 rpm, 90 V, 5.4 amps, 60 Hz, single phase. Hub City Motor Drive, ratio: 400, 4.3 rpm (final). Inlets: (2) 1 $\frac{1}{2}$ in. dia. FNPT, (1) 1 in. dia. quick connect fitting. Outlets: (2) 2 in. dia. FNPT (drain ports), (1) 2 in. dia. FNPT (overflow). Overall dimensions: 4 ft. 4 in. L x 3 ft. W x 5 ft. H.





SERIAL NO.	LZ-58936-3	
MODEL NO.		BAS
SIZE	20 IN X 24 IN	CAP
TYPE/HAND	ROTARY DRUM R.H.	RATI



RELIANCE	
POWER MATCHED/R.P.M. RECTIFIED POWER MOTOR	
IDENTIFICATION NO T56G3205M-XG	
TYPE TR.	FR. U56HC
HP. 1/2	R.P.M. 1725
ARM. VOLTS	90
FIELD VOLTS	50/100
ARM. AMPS.	5.4
FIELD AMPS	1.28/1.64
FORM FACTOR	1.30
INSUL. CLASS.	F
MAX. AMB. TEMP.	40 °C
TIME RATING	CONT
E04825 1AT RWR 012 K	

HUB CITY		
ERDEEN, SO. DAK. 57401 USA		
02-20-28170-3206		
ASSEMBLY NUMBER		
3206	400	1.00
MODEL	RATIO	STYLE
WARNING		
SHIELD ALL MOVING PARTS BEFORE OPERATING		