

Vilter 8-Cylinder Reciprocating Compressor

Mfg: Vilter

Model: 458

Stock No. MSST004.

Serial No. 18945

Vilter 8-Cylinder Reciprocating Compressor. Model:458. S/N: 18945. 5 in. stroke travel. Refrigerant: R-717. Liquid-cooled heads. Westinghouse Motor, 100 hp, 1180 rpm, 230/460 V, 232/116 amps, 60 Hz, 3 phase. Inlet: (1) 5 in. dia. suction port. Outlets: (1) 4 in. dia. discharge port. Overall dimensions: 7 ft. 8 in. L x 3 ft. 4 in. W x 4 ft 2 in. H.





