


# Capacity / WHP / VHP / NIPR



## Universal I Sanitary Pumps Model **006**

Alloy 88 Rotors  
Standard Clearance  
Standard Port Size = 1.0"  
Displacement =  
0.0082 Gal/Rev

**BHP = WHP + VHP**




**Waukesha  
Cherry-Burrell**

611 Sugar Creek Road  
Delavan, WI 53115 USA  
Tel: 1-800-252-5200 or 262-728-1900  
Fax 1-800-252-5012 or 262-728-4904  
E-mail: [custserv@gowcb.com](mailto:custserv@gowcb.com)  
Web Site: <http://www.gowcb.com>

Effective Date: 3-16-2000  
Specifications subject  
to change without notice

Curve Number  
**95-07133**



|           | A    | AO   | B    | CP    | CP1   | CP4   | D    | E    | F    | G         | I    | J    | L    | O    | U     | X    | 2X   |
|-----------|------|------|------|-------|-------|-------|------|------|------|-----------|------|------|------|------|-------|------|------|
| <b>IN</b> | 4.75 | 8.30 | 3.75 | 12.04 | 13.47 | 15.25 | 5.50 | 1.94 | 2.31 | .41, SLOT | 7.66 | 2.93 | 9.61 | 4.21 | 0.875 | 3.49 | 6.97 |
| <b>MM</b> | 121  | 211  | 95   | 306   | 342   | 387   | 140  | 49   | 59   | 10, SLOT  | 194  | 74   | 244  | 107  | 22    | 89   | 177  |

CP= Standard Cover, CP1= Jacketed Cover, CP4= Manual Vented Cover, Connection sizes for Jacketed Covers are ¾"-14 NPT on Models 006-UI to 030-UI, 1"-11-½ NPT on Models 060-UI and 130-UI.

Dimension 'X' and '2X' apply for Bevel