

W. A. Kates Co. Flow Rate Control Valve

Mfg: W. A. Kates Co.

Model: LB11B-A

Stock No: NOI1026

Serial No: 37677

W.A. Kates Co. Flow Rate Control Valve. Model: LB11B-A. S/N: 37677. Body: stainless steel. Trim: stainless steel. Max internal W. P: 275 P.S.I.G. at 100 °F. Diff pressure regulating band 150 P.S.I. Inlet/outlet: (2) 3 in. S-line. Overall dimensions: 1 ft. 10 in. L x 1 ft. 4 in. W x 2 ft. 2 in. H.





9/86

KATES

TFA 2796 4



346