

Conveyor

Mfg:


Model:

Stock No: NOI1119

Serial No:

Conveyor. U.S. Electrical motor: .75 hp, 1750 rpm, 208-230/460 v, 2.8-2.8/1.4 a, 60 Hz, 3 phase. U.S. Electrical motor drive: 1 max input hp, 966 max output torque. Belt dimensions: 11 ft. 6 in. L x 11-3/4 in. W. Overall dimensions: 5 ft. 11 in. L x 2 ft. W x 3 ft. 4 in. H.





MOTORIS
SYNCHRO GEAR MODULE
 ALL ELECTRICAL MOTORS
 DIVISION OF EMERSON ELECTRIC CO.
 ST. LOUIS, MO
 FRAME 6 TYPE UTP RATIO 33.0
 MAX INPUT HP 1.00 @ 1750 RPM
 MAX OUTPUT TORQUE 966 @ 45 RPM
 MOD # E436/B076270A

UNIMOTOR
 MODEL E183A HP .75 PH 3 HZ 60 RPM 1750
 FRAME 56 TYPE UTP ENCL TTT 1.3 CODE M
 VOLTS 208-230/460 MAX AMB 40
 FLAMPS 2.8-2.8/1.4 SHAFT END BRG
 I/F AMPS 3.2/1.6 IOP END BRG
 C01-E183-M
 AMPS MAX AT 1750 RPM