

Scotsman Flake Ice Maker Cabinet

Mfg: Scotsman

Model: AFE325AS-1A

Stock No: NOI1310

Serial No: 0511320013712

Scotsman Ice Maker. Model: AFE325AS-1A. Serial: 0511320013712. Maximum ice production: 324 lbs per 24 hours. Ice Type: Flake. Storage capacity: 140 lbs. Air temperature: 50-100°F. Water temperature: 40-100°F, 20-80 PSI. Electrical Supply: 115 Volts, 10.7 Amp, 60 Hz, 1-Phase. Compressor 115 Volts, 5.6 RL/FLA, 40.0 LRA. Fan 115 Volts, .48 RLA/FLA, 6 W/HP, Auger Drive 115 Volts, 3.2 RLA/FLA, 1/10 W/HP. Refrigerant: R-134, 11 OZ, 311 Grams. Design Pressure: Low-140 PSI, High-260 PSI. Inside Dimensions: 21 in. L x 21 in. W x 20 in. H. Approximate weight: 215 lbs. Outside Dimensions: 36 in. L x 24 in. W x 38 in. H. (ACN32).



