

Eriez Magnetics Hi-Vi Vibrator Feeder

Mfg: Eriez Magnetics

Model: 65B

Stock No.: NOI8035

Serial No.: PP03 170

Eriez Magnetics Hi-Vi Vibrator Feeder. Model: 65B, S/N: PP03 170. Feeder provides a wide capacity range to feed controlled amounts from a few pounds to 140 tons/hr (127 metric tons/hr), when properly installed at a 6° down slope, and even more if operated with more down slope and skirt boards (capacity based on 24 in. x 30 in. tray properly installed with skirt boards). Rugged construction makes this an ideal unit for handling abrasives, slag, coal, ores, grains, or wherever controlled feeding of large tonnages is required. This Eriez heavy duty suspended feeder may be mounted in any of the following ways: suspended from cables attached to the suspension bracket eye bolts (located in the front and rear), floor mounted with floor mounting accessories, and any combination of suspension and floor mounting. Electrical requirements: 115 V, 15.0 amps, 60 Hz. Shaker tray dimensions: 40 in. L x 24 in. W. Inlets: 24 in. W x 6 in. H. Outlets: 17 in. W x 6 in. H. Overall dimensions: 5 ft. 2 in. L x 3 ft. 3 in. W x 3 ft. 2-1/2 in. H.



