

Pneumatech Non-Cycling Refrigeration Air Dryer

Mfg: Pneumatech

Model: ADW-1000

Stock No: NOI8054

Serial No: 9505-T120700-68545

Pneumatech Non-Cycling Refrigeration Air Dryer. Model: ADW-1000. S/N: 9505-T120700-68545. Capacity: 1,000 SCFM. Compressor: 5 hp. 440/480 V, 60 Hz, 3 Phase. Compressor: RLA: 9.50 LRA: 62.0. Max air pressure: 150 psig. Max inlet air temp: 100°F. Max ambient temp: 100°F. Min. ambient temp: 55°F. Min circuit ampacity: 11.88. Refrigerant type: R-22. Max fuse or circuit breaker size: 20 amps. Factory refrigerant charge: 18 lbs. refrigerant max pressure: low side: 150 psig - high side 350 psig. Inlets: 3 in. flanged port. Outlets: 3 in. flanged port. Overall dimensions: 5 ft. L x 3 ft. W x 5 ft. H.





