

Stainless Steel Paraflash Separator

Mfg:

Model:

Stock No: NOI9014

Serial No:

Stainless Steel Paraflash Separator. Approximate volume: 59 ft.³. Inside dimensions: 41-3/4 in. dia. x 5 ft. 1 in. straight wall. (2) 4 in. sight glass windows. (1) 3 in. stainless steel sprayball. Inlets/outlets: (1) 1 ft. 6 in. dia. manway port. (1) 9-3/4 in. flange dia. (12) 1 in. mounting holes, 3-5/8 in. adjacent, 1 ft. 2-1/4 in. opposite. (1) 4 in. flange dia. (8) 3/4 in. mounting holes, 2-3/4 in. adjacent, 7-1/2 in. opposite. (1) 2 in. FNPT. (1) 1-1/2 in. port. (1) 3/4 in. FNPT. (1) 3/8 in. MNPT. Overall dimensions: 6 ft. 1 in. L. x 5 ft. 5-1/4 in. W. x 12 ft. 7 in. H.





