

## Viking Positive Displacement Pump

Mfg: Viking


Model: AV476


Stock No: NOIP1006

Serial No: 11725555

Viking Positive Displacement Pump. Model: AV476. S/N: 11725555. Flow rate for new pump is 50 gpm with required horsepower and pressure. (1) 3-1/4 in. rotor. Inlet/outlet: (2) 2-5/8 in. Overall dimensions: 1 ft. 3 in. L x 10-1/2 in. W x 10 in. H.







YORK, PA., USA

1-800-888-4037

SER # 11725555

FES P/N 290-000030-022