

Viking Positive Displacement Pump

Mfg: Viking

Model: AS195

Stock No: NOIP1008

Serial No: 1072382

Viking Positive Displacement Pump. Model: AS195. S/N: 1072382. Flow rate for new pump is 40 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. General Electric motor: 5 hp, 1160 rpm, 230/460V, 16.4/8.2 a, 60 Hz, 3 phase. (1) 3-1/2 in. rotor. Inlet/outlet: (2) 2-3/4 in. FNPT. Overall dimensions: 3 ft. 4 in. L x 1 ft. 2 in. W x 1 ft. 3 in. H.





