

## Viking Positive Displacement Pump

**Mfg: Viking**

**Model: AK195**

**Stock No: NOIP1009**

**Serial No: 1067671**

Viking Positive Displacement Pump. Model: AK195. S/N: 1067671. Flow rate for new pump is 50 gpm with required horsepower and pressure. General Electric motor: 5 hp, 1160 rpm, 230/460 v, 16.4/8.2 a, 60 Hz, 3 phase. (1) 3-1/2 in. rotor. Inlet/outlet: (2) 2-3/4 in. FNPT. Overall dimensions: 3 ft. L x 1 ft. 3 in. W x 1 ft. 3 in. H.



