

Sherwood Positive Displacement Pump

Mfg: Sherwood

Model:

Stock No: NOIP1115

Serial No:

Sherwood Positive Displacement Pump. Baldor Industrial motor: 1-.44 hp, 1725/1140 rpm, 460 v, 1.9/1.4 a, 60 Hz, 3 phase. (2) 1-1/4 in. L x 1-3/4 in. rotors. Inlet/outlet: (2) 3/4 in. FNPT. Overall dimensions: 1 ft. 7 in. L x 10 in. W x 11-1/2 in. H.



