

## Vertical Sump Pump

**Mfg:**

**Model:**

**Stock No: NOIP1118**

**Serial No:**

Vertical Sump Pump. Reliance Electric motor: 3/4 hp, 1725 rpm, 230/460 v, 3.44/1.72 a, 60 Hz, 3 phase. (1) 5 in. dia. impeller. Inlet/outlet: (1) 1-1/2 in. port, (1) 1-1/2 in. FNPT. Overall dimensions: 1 ft. 1 in. L x 8 in. W x 2 ft. H.





