

## APV R6 Positive Displacement Pump

**Mfg: AVP**

**Model: 6UR**

**Stock No: NOIP1201**

**Serial No: B-2971**

APV R6 Positive Displacement Pump. Model 6UR. S/N: B-2971. Flow rate for a new pump is 120 gpm at max rpm of 900. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Pump has O-ring seals. Drive can be changed to suit your application. SEW Eurodrive gearmotor. Motor: 3 hp, 230/460 V, 8.6/4.3 amps, 1700 rpm, 60 Hz, 3 phase. Gearbox: 12.50 ratio, 136 rpm final. Inlet/outlet: (2) 2-1/2 in. bevel seat fittings. Overall dimensions: 3 ft. 6 in. L x 1 ft. 5 in. W x 3 ft. 6 in. H.







