

Moyno Progressing Cavity Pump

Mfg: Moyno

Model: 2L4 SSQ AAA

Stock No. NPPC125

Serial No. AM16862-1

Moyno Progressing Cavity Pump. Model: 2L4 SSQ AAA. S/N: AM16862-1. Displacement per revolution: 5.20 gal/100 rev. Capacity: 8.02 gpm. Baldor Industrial Motor, 3 hp, 1,760 rpm, 230/460 V, 5.6/2.8 amps, 60 Hz, 3 phase. Dodge AGP Motor Drive, 11.4 ratio, 154.38 rpm (final), 1394 in. lbs. torque. Inlets: (1) 2-1/2 in. dia. inlet with a 7 in. dia. flange and (4) 5/8 in. dia. attachment holes at a center-to-center distance of 4 in. Outlets: (1) 2 in. dia. NPT (female). Overall dimensions: 84 in. L x 19 in. W x 16 in. H.

