

Moyno Progressing Cavity Pump

Mfg: Moyno

Model: 2L6-SSQ

Stock No: NPPC127

Serial No: 54910-5-91

Moyno Progressing Cavity Pump. Model: 2L6-SSQ. S/N: 54910-5-91. Motor drive: 11.30 input hp, 6.2 ratio, 2441 in/lb torque capacity, 1750 in rpm, 280 out rpm. Screw worm dimensions: 2 ft. L x 2-1/2 in. diameter. Inlets: (1) 3 in. dia. flanged port. Outlets: (1) 2-1/2 in. dia. FNPT. Overall dimensions: 6 ft. 10 in. L x 1 ft. 6 in. W x 1 ft. 2 in. H.



