

Mix/Blend Tank-30 Gallon

Mfg:

Model:

Stock No. OI113

Serial No.

Mix/Blend Tank-30 Gallon.

- Inside dimensions: 19-1/2 in. W, 24 in. H.
- Inlets: (1) 1 in. with ball valve.
- Outlets: (1) 1-1/2 in. with pump.
- Stands on a frame with motor, pump and control box.
- Frame has 2 wheels and 2 casters (6 in. diameter), and stand 7 in. off the ground.
- Maja, Asynkron Motor, 260/460 V, 3 phase, 4.8/2.8 amps, 60 Hz, 3,500 rpm.
- Pump: Majmar, Type CR 4.40N, Model: 3086, Q (M3/H): 4.8, H (M): 49.

