

Wolfking Danmark Screw Auger Conveyor with Hopper

Mfg: Wolfking Danmark

Model:

Stock No. OI162.

Serial No. 58458

Wolfking Danmark Screw Auger Conveyor with Hopper. Type: Horizontal. S/N: 58458. Maximum capacity: 2.46 cu. ft. Minimum capacity: 0.73 cu. ft. Screw auger dimensions: 10 in. dia. x 72 in L. Screw auger housing diameter: 10-1/4 in. Flender Motor, 5.5 kW, 1728 rpm, 220 V, 3 phases. Gear Drive, no nameplate information. Inlets: (1) 51 in. L x 19 in. W infeed hopper. Outlets: (1) 10-1/4 in. dia. discharge. Overall dimensions: 84 in. L x 35 in. W x 32 in. H.

