

**AEC Nelmor Co Inc. Grinder / Hammermill – 30 HP**

**Mfg: AEC Nelmor Co Inc.**

**Model:**

**Stock No: OI169**

**Serial No:**

AEC Nelmor Co Inc. Grinder / Hammermill. Unit has a hopper infeed equipped with spray bridge. Infeed height: 74 in. Hammermill has rotating blades that reduce particle size until they pass through the screen hole size. Mounted on a stainless steel frame. Lincoln AC Motor, 30 hp, 1760 rpm, 90 rpm (final), 230/460 V, 74/37 amps, 60 Hz, 3 phase. Inlets: 14 in. L x 24 in. W. Outlets: 4 in. dia. flanged discharge. Overall dimensions: 4 ft. 11 in. L x 4 ft. 3 in. W x 10 ft. 2 in. H.







