

Allen Bradley 20 HP Variable Frequency Inverter Drive

Mfg: Allen Bradley

Model: 1336

Stock No. OI174.

Serial No.

Allen Bradley 20 HP Variable Frequency Inverter Drive. Model: 1336. Cat. No: 1336S-B020-AN-EN4-L6. AC Input (constant torque): 22.5-26.8 hp (21-25 KVA), 380-480 V, 32 amps, 50/60 Hz, 3 phase. AC output (constant torque): 22.5 hp (21 KVA), 0-460 V, 31 amps, 0-400 Hz, 3 phase. AC input (variable torque): 24.6-31.6 hp (23-29 KVA), 380/460 V, 35 amps, 50/60 Hz, 3 phase. AC output (variable torque): 28.9 hp (27 KVA), 0-460 V, 34 amps, 0-400 Hz, 3 phase. Previously used by Yoplait. Overall dimensions: 17-1/2 in. L x 9-1/2 in. W x 21-1/2 in. H.

