

Brooks Wafer-Mag Magnetic Flowmeter

Mfg: Brooks

Model: 7482B1W1C4AA

Stock No. OI210.

Serial No. 8811-9718

Brooks Wafer-Mag Magnetic Flowmeter. Model: 7482B1W1C4AA. S/N: 8811-9718. K-Factor: 49379.943 PPG. Maximum pressure: 740 psig @ 100 °F. Maximum power: 15 Watts. Maximum process temperature: 30 °F. Overall dimensions: 9-1/2 in. L x 6-1/2 in. W x 8-1/2 in. H.



