

Brooks Wafer-Mag Magnetic Flowmeter

Mfg: Brooks

Model: 7485C1A1C6AAAA

Stock No. OI211.

Serial No. 9107-12547

Brooks Wafer-Mag Magnetic Flowmeter. Model: 7485C1A1C6AAAA. S/N: 9107-12547. K-Factor: 21082.212 PPG. Maximum process pressure: 740 psi @ 100 °F. Maximum process temperature: 300 °F. Power requirements: 115 VAC, 50/60 Hz. Flowtube inlets/outlets: (2) 1/2 in. dia. lapped flanges. Overall dimensions: 9-1/2 in. L x 6-1/2 in. W x 10-1/2 in. H.

