

Brooks Wafer-Mag Magnetic Flowmeter

Mfg: Brooks

Model: 7401C1W1C6AA

Stock No. OI213.

Serial No. 9003-15772 and 9003-15773

(2) Brooks Wafer-Mag Magnetic Flowmeter. Model: 7401C1W1C6AA. S/N's: 9003-15772 and 9003-15773. K-Factor: 7151.33PPG. Maximum process pressure: 740 psi @ 100 °F. Maximum process temperature: 300 °F. Power requirements: 115 VAC, 50/60 Hz. Flowtube inlets/outlets: (2) 1 in. dia. lapped flanges. Overall dimensions: 10-1/2 in. L x 6-1/2 in. W x 11 in. H.



