

## Goulds Centrifugal Pump

Mfg: Goulds

Model: 3196

Stock No. OIP049.

Serial No. 788B856

Goulds Centrifugal Pump. Model: 3196, S/N: 788B856. Inlet: 1-1/2 in. Outlet: 1 in. Max impeller diameter 6 in. Impeller diameter: 4.75 in. Material construction: Alloy 20. Double mechanical seals with flushing. US Motor: 5 hp, 3450 rpm, 230/460 V, 13.3/6.7 amps, 60 Hz, 3 phase. Overall dimensions: 40 in. L x 13 in. W x 19 in. H.

