

Bran & Lubbe High Pressure Pump

Mfg: Bran & Lubbe

Model:

Stock No.:OIP064

Serial No.:

Bran & Lubbe High Pressure Pump. 2 in. dia. plungers. Tapered seat ball valves. Reliance Electric Motor, 40 hp, 1775 rpm, 460 V, 47.7 amps, 60 Hz, 3 phase. Flender Motor Drive, 1.9 ratio, 286 rpm (output). Inlets: (1) 2 in. dia. S-Line. Outlets: (1) 2 in. dia. S-Line. Overall dimensions: 5 ft. 2 in. L x 4 ft. 7 in. W x 4 ft. 7 in. H.





