

Peerless Pump

Mfg:

Model:

Stock No. OIP067.

Serial No.

Peerless Pump. Type: 1025A. Imp: 2634314. Pump capacity: 420 gpm @ 65 ft. Impeller diameter: 10 in. WEG motor, 10 hp, 1750 rpm, 230/460 V, 28/14 amps, 60 Hz, 3 phases. Design: DB. Flange: 7 in. and (4) 3/4 in. holes with 5-1/2 in. center to center. Flange: 7-1/4 in. and (4) 1/2 in. holes fpt. with 6 in. center to center. Inlet: 3 in.; outlet: 2-1/2 in. Overall dimensions: 23 in. L x 16-1/2 in. W x 15 in. H.



