

Crane Centrifugal Pump

Mfg: Crane

Model: 3062 0925

Stock No.: OIP084

Serial No.: DC-564970

Crane Centrifugal Pump. Model: 3062 0925. S/N: DC-564970. Flow rate for new pump is 48 gpm with required horsepower and 31 TDH. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum speed: 1750 rpm. Impeller diameter: 6 in. Baldor Industrial Motor, 1.5 hp, 1725 rpm, 208-230/460 V, 5.3-5.3/2.5 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. 125 lb. ANSI flange. Outlets: (1) 1 in. dia. 125 lb. ANSI flange. Overall dimensions: 3 ft. 4 in. L x 1 ft. 1 in. W x 1 ft. 3 in. H. (ACN35a)



