

Tri-Flo C218 Centrifugal Pump

Mfg: Tri-Flo

Model: C218 MD21T-S

Stock No. OIP086.

Serial No. 166095-01

Tri-Flo C218 Centrifugal Pump. Model: C218 MD21T-S. S/N: 166095-01. Capacity: 15 gpm @ 325 t.d.h. Impeller diameter: 8 in. Baldor Industrial Motor, 10 hp, 3450 rpm, 208-230/460 V, 25-24/12 amps, 60 Hz, 3 phase. C-series pumps deliver dependable performance under any low-viscosity application. They feature a practical low maintenance design and can handle viscous products at elevated GPM and pressure ratings. Applications include: pharmaceutical, biotechnology, fine chemical, food and beverage industries. Inlet: 3 in. dia. S-Line port. Outlet: 1-1/2 in. dia. S-Line. Overall dimensions: 24-1/2 in. L x 12 in. W x 12-1/2 in. H.



